

Project:		
Fixture Type:		
Location:		
Contact:		

# 6IN RECESSED SLOPE Ceiling joists, or in suspended ceilings Mounted • Damp Location Listed

#### **Description:**

6" Recessed Slope Ceiling Remodel Non-IC Housing for 6" Trim

#### **Specifications:**

- The housing is constructed from die-formed corrosion resistant galvanized steel
- Its gasketed Air-Tight housing restricts airflow from conditioned spaces into unconditioned attic space, preventing unnecessary HVAC costs and improving the overall home energy efficiency
- An integral flange and locking springs create a snug fit against the ceiling, permitting quick mounting in 1/2 in. to 1-1/2 in. thick ceilings
- The socket position can be adjusted to accommodate ceiling pitches from 2/12 to 7/12 pitch
- Wiring is made easy with the included wiring quick-connects that allow simple installation of 12-20 AWG wire without using separate wire nuts - simply strip supply wires and push in
- Housing is provided with a medium base socket for a variety of bulbs which are based on the trim used.
- · Housing features a universal J-box with snap-out sides
- CULus damp location rating makes this trim ideal for use in a variety of room settings and is thermally protected against improper use of lamps
- · Fully dimmable with dimmable bulbs

#### **Performance:**

Input Power	100 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed

## P806A-R-MD-AT



#### **Dimensions:**

Length: 6-1/2 in Width: 13-1/8 in Height: 8-3/16 in

### **Compatible housing and lamp information:**

	NON IC		IC	
TRIM	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
	BR30	100W		
P800020-028	R30	100W		
P806005-028	A19	60W		
P806004-028	A19	60W		
0	BR30	100W		
P806008-028 P806008-031 P806008-020	R30	100W		
	PAR30L	75W		