

| Project: | | | | |
|----------|------|--|--|--|
| Fixture | Туре | | | |

Location:

Contact:

6IN RECESSED

Ceiling joists, or in suspended ceilings Mounted • Damp Location Listed

Description:


6 Recessed New Construction Housing with Quick Link Connector for 6" Trim

Specifications:

- The housing and frame are constructed from die-formed corrosion resistant galvanized steel
- Its gasketed air-tight lamp housing prevents conditioned air from escaping into the attic space, reducing unnecessary HVAC energy usage, and the lamp housing compartment can be adjusted to fit ceiling thicknesses from ½ in. to 1 ¼ in.
- Wiring is made easy with the included wiring quick-connects that allow simple installation of 12-20 AWG wire without using separate wire nuts simply strip supply wires and push in
- Bar hangers have a maximum span of 24 in. and are scored in two locations for fast, clean breaking, allowing housing installation in very narrow joist spacings, and Includes pre-installed framing nails on the bar hangers, making installation quick and efficient and the hanger bars include t-bar mounting clamps for use in suspended t-grid ceilings
- Features a universal J-box with snap-out sides
- Uses 1 BR40 light source (sold separately) 90-watt maximum
- $\boldsymbol{\cdot}\,$ The housing is compatible with a variety of trims and finishes
- CULus damp location rating makes this trim ideal for use in a variety of room settings where
 water may be present
- Fully dimmable with dimmable bulbs

Compatible housing and lamp information:

| | NON IC | | іс | |
|----------------------------|------------|-----------|------------|-----------|
| TRIM | LAMP SHAPE | MAX WATTS | LAMP SHAPE | MAX WATTS |
| \bigcirc | BR30 | 65W | BR30 | 65W |
| P800020-028 | R30 | 75W | R30 | 75W |
| | BR40 | 90W | BR40 | 90W |
| | PAR38 | 90W | PAR38 | 90W |
| | BR30 | 65W | BR30 | 65W |
| P806000-028 | R30 | 75W | R30 | 75W |
| P806000-031 P806000-020 | PAR30 | 75W | PAR30 | 75W |
| | PAR30L | 75W | PAR30L | 75W |
| | BR40 | 90W | BR40 | 90W |
| | PAR38 | 90W | PAR38 | 90W |
| | BR30 | 65W | BR30 | 65W |
| P806002-028 | R30 | 75W | R30 | 75W |
| | PAR30 | 75W | PAR30 | 75W |
| | PAR30L | 75W | PAR30L | 75W |
| | PAR38 | 90W | PAR38 | 90W |
| | BR30 | 65W | BR30 | 65W |
| P806001-028 P806001-031 | R30 | 75W | R30 | 75W |
| | PAR30 | 50W | PAR30 | 50W |
| | PAR30L | 75W | PAR30L | 75W |
| | PAR38 | 90W | PAR38 | 90W |
| | BR30 | 65W | BR30 | 65W |
| | R30 | 75W | R30 | 75W |
| P806003-028 | PAR30 | 50W | PAR30 | 50W |
| | PAR30L | 75W | PAR30L | 75W |
| P806005-028 | A19 | 40W | A19 | 40W |
| P806004-028 | A19 | 40W | A19 | 40W |



P806N-N-MD-ICAT



Performance:

| Input Power | 90 W |
|---------------|----------------------------|
| Input Voltage | 120 VAC |
| Warranty | 1-year Limited Warranty |
| Labels | cULus Damp Location Listed |

Dimensions:

Length: 6-5/8 in Width: 9-3/8 in Height: 7-3/8 in

Compatible LED trim information:

| PAIR WITH THESE TRIMS | | | | |
|-----------------------|----------------|--|--|--|
| 0 | P800002-028-30 | | | |
| | P800018-028-CS | | | |
| | P800019-028-CS | | | |
| | HS56-WH-30K9 | | | |
| | P800021-028-30 | | | |

www.progresslighting.com