

| Project:      |
|---------------|
| Fixture Type: |

Location:

Contact:

# **6IN RECESSED**

Ceiling joists, or in suspended ceilings Mounted • Damp Location Listed

#### **Description:**

6" Recessed Remodel Housing for 6" Trim

## Specifications:

- The housing and frame are constructed from die-formed corrosion resistant galvanized steel
- An integral flange and locking springs create a snug fit against the ceiling, permitting quick mounting in 1/2 in. to 1-1/2 in. thick ceilings
- Wiring is made easy with the included wiring quick-connects that allow simple installation of 12-20 AWG wire without using separate wire nuts simply strip supply wires and push in
- Housing is thermally protected against improper use of lamps
- · Features a universal J-box with snap-out sides
- Uses 1 BR40 light source (sold separately) 90-watt maximum
- · This housing is perfect for those with limited or no access to above the ceiling
- It is cULus damp location listed and can be used in areas where water is present
- Fully dimmable with dimmable bulbs

#### **Performance:**

| Input Power   | 90 W                       |
|---------------|----------------------------|
| Input Voltage | 120 VAC                    |
| Warranty      | 1-year Limited Warranty    |
| Labels        | cULus Damp Location Listed |

#### Compatible housing and lamp information:

|                            | NON IC     |           | іс         |           |
|----------------------------|------------|-----------|------------|-----------|
| TRIM                       | LAMP SHAPE | MAX WATTS | LAMP SHAPE | MAX WATTS |
|                            | R30        | 75W       | R30        | 75W       |
| P800020-028                | PAR30      | 75W       | PAR30      | 75W       |
|                            | R40        | 85W       | R40        | 85W       |
|                            | PAR38      | 90W       | PAR38      | 90W       |
| P806000-028                | R30        | 75W       | R30        | 75W       |
| P806000-031<br>P806000-020 | PAR30      | 75W       | PAR30      | 75W       |
|                            | R40        | 85W       | R40        | 85W       |
|                            | PAR38      | 90W       | PAR38      | 90W       |
| P806002-028                | R30        | 75W       | R30        | 75W       |
|                            | PAR30      | 75W       | PAR30      | 75W       |
|                            | R40        | 85W       | R40        | 85W       |
| P806001-028<br>P806001-031 | PAR38      | 90W       | PAR38      | 90W       |
|                            | R30        | 75W       | R30        | 75W       |
|                            | PAR30      | 75W       | PAR30      | 75W       |
|                            | R40        | 85W       | R40        | 85W       |
| P806003-028                | PAR38      | 90W       | PAR38      | 90W       |
|                            | R30        | 75W       | R30        | 75W       |
|                            | PAR30      | 75W       | PAR30      | 75W       |
| P806005-028                | A19        | 40W       | A19        | 40W       |
| P806004-028                | A19        | 40W       | A19        | 40W       |

# P806N-R-MD-ICAT



#### **Dimensions:**

Length: 7-3/16 in Width: 12-15/16 in Height: 7-3/8 in

## **Compatible LED trim information:**

| PAIR WITH THESE TRIMS |                |  |  |  |
|-----------------------|----------------|--|--|--|
| 0                     | P800002-028-30 |  |  |  |
| 0                     | P800018-028-CS |  |  |  |
|                       | P800019-028-CS |  |  |  |
|                       | HS56-WH-30K9   |  |  |  |
|                       | P800021-028-30 |  |  |  |