

Project: Fixture Type:

Location

Contact:

## 6IN RECESSED SHALLOW Ceiling jo

Ceiling joists, or in suspended ceilings Mounted • Damp Location Listed

#### **Description:**

6" Recessed Shallow New Construction Housing with Quick Link Connector for 6" Trim

#### **Specifications:**

- $\boldsymbol{\cdot}$  The housing and frame are constructed from die-formed corrosion resistant galvanized steel
- Its gasketed air-tight lamp housing prevents conditioned air from escaping into the attic space, reducing unnecessary HVAC energy usage, and the lamp housing compartment can be adjusted to fit ceiling thicknesses from ½ in. to 1 ¼ in.
- Wiring is made easy with the included wiring quick-connects that allow simple installation of 12-20 AWG wire without using separate wire nuts simply strip supply wires and push in
- The housing has pre-installed nails on the adjustable hanger bars which are easily installed in regular lumber, engineered lumber, and laminated beams
- Hanger bars include t-bar mounting clamps for use in suspended t-grid ceilings and the bar hangers have a maximum span of 24 in. and are scored in two locations for fast, clean breaking, allowing housing installation in very narrow joist spacings
- Housing is provided with a medium base socket for a variety of bulbs which are based on the trim used.
- The housing is compatible with a variety of trims and finishes to create different lighting effects or to easily match any decor
- CULus damp location rating makes this trim ideal for use in a variety of room settings where
  water may be present
- Fully dimmable with dimmable bulbs

#### **Performance:**

Input Power	50 W
Input Voltage	120 VAC
Warranty	1-year Limited Warranty
Labels	cULus Damp Location Listed

#### Compatible housing and lamp information:

	NON IC		IC	
TRIM	LAMP SHAPE	MAX WATTS	LAMP SHAPE	MAX WATTS
	BR30	50W	BR30	50W
P800020-028	R30	50W	R30	50W
	PAR30	50W	PAR30	50W
P806005-028	A19SBLED	10W	A19SBLED	10W
P806004-028	A19SBLED	10W	A19SBLED	10W
	BR30	50W	BR30	50W
P806006-028	R30	50W	R30	50W
P806006-031	PAR30	50W	PAR30	50W
	BR30	50W	BR30	50W
P806007-028	R30	50W	R30	50W
	PAR30	50W	PAR30	50W

# P806S-N-MD-ICAT



#### **Dimensions:**

Length: 6-1/2 in Width: 9-3/8 in Height: 5-1/2 in

### Compatible LED trim information:

PAIR WITH THESE TRIMS		
0	P800002-028-30	
0	P800018-028-CS	
0	P800019-028-CS	
	HS56-WH-30K9	
0	P800021-028-30	

/01 Millennium Blvd. Greenville, South Carolina 2960/