

Everlume

Project:
Fixture Type:

Location:
Contact:

• Wet Location Listed PROGRESS LED

## **Description:**

Everlume Collection 4 in. Satin White LED Low Profile Canless Recessed Downlight

## **Specifications:**

- · Dimmable to 10% brightness (See Dimming Notes)
- · Americans With Disabilities Act (ADA) compliant

#### **Performance:**

Input Power	10 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	825/82 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Wet Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2019
	IC Rated






# **Dimensions:**

Diameter: 4-3/4 in Height: 1-1/8 in



# Everlume



#### **Dimming Notes:**

P807000-028-30 is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

## **Dimming Controls:**

Leviton\_6681

Leviton\_6672

Lutron\_NTEVL-300

Lutron\_DVELV-300P

Lutron\_DVCL-253P

Lutron\_Caseta Wireless

Lutron\_AYCL-153P

Lutron\_TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P807000-028-30