

## Everlume

• Wet Location Listed **PROGRESS LED**

### Description:

---

Everlume Collection 6 in. Satin White LED Low Profile Canless Recessed Downlight

### Specifications:

---

- Dimmable to 10% brightness (See Dimming Notes)
- Americans With Disabilities Act (ADA) compliant

### Performance:

---

Input Power	12 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	950/79 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed Meets California Title 24 JA8-2019 IC Rated

# P807001-028-30



### Dimensions:

---

Diameter: 7-1/8 in  
Height: 1 in

# P807001-028-30

## Dimming Notes:

---

P807001-028-30 is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

## Dimming Controls:

---

Eaton\_AAL06

Eaton\_SAL06P

IDevices\_IDEV009

Leviton\_6681

Leviton\_IPI06-1LZ

Leviton\_6672

Leviton\_6674

Lutron\_NTEVL-300

Lutron\_DVELV-300P

Lutron\_DVCL-253P

Lutron\_Caseta Wireless

Lutron\_AYCL-153P

Lutron\_SCL-153P

Lutron\_TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.