

Everlume

• Wet Location Listed PROGRESS **LED**

Description:

Everlume Collection 6 in. Satin White Low Profile Canless Recessed Downlight

Specifications:

- Dimmable to 10% brightness (See Dimming Notes)
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	12 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	925/77 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed Meets California Title 24 JA8-2019 IC Rated

P807003-028-30



Dimensions:

Diameter: 7-1/8 in
Height: 1 in

P807003-028-30

Dimming Notes:

P807003-028-30 is designed to be compatible with many ELV/Reverse Phase Triac/Forward Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton_AAL06

Eaton_SAL06P

IDevices_IDEV009

Leviton_6681

Leviton_IPI06-1LZ

Leviton_6672

Leviton_6674

Lutron_NTEVL-300

Lutron_DVELV-300P

Lutron_DVCL-253P

Lutron_Caseta Wireless

Lutron_AYCL-153P

Lutron_SCL-153P

Lutron_TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.