

Project:
Fixture Type:

Location:
Contact:

Intrinsic

Ceiling Mounted • Damp Location Listed PROGRESS LED



Description:

P810029-028-30

Specifications:

- · Dimmable to 10% brightness (See Dimming Notes)
- · Mounting strap for outlet box included
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	15.5 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,000/64 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2016



Dimensions:

Length: 7-1/4 in Diameter: 7-1/4 in Height: 1-1/2 in



Intrinsic

Ceiling Mounted • Damp Location Listed PROGRESS LED



Dimming Notes:

P810029-028-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

P810029-028-30

Dimming Controls:

Eaton AAL06

Eaton SAL06P

IDevices IDEV009

Leviton 6681

Leviton IPI06-1LZ

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron Caseta Wireless

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.