


Accessory

12 Volt Manual Transformers

Landscape

Туре	
-31	
P8590 🗆	
P8591 🖳	
P8592 □	

	Finish						Dimensions (Inches)		
Catalog No.	Black	Wattage	Manual	Timer	Photocell	Α	В	С	
P8590	-31	150	Yes	No	No	3-1/2	3	8-3/4	
P8591	-31	300	Yes	No	No	4	5	10	
P8592	-31	600*	Yes	No	No	4	4-1/2	12	



*2/300w circuits

Specifications:

Electrical

- 300 and 600 watt units only
- Maximizes light output and lamp life under varying load conditions
- Adjusts for light loss in longer runs
- Isolation type transformer for safe operation
- Three foot 12 gauge cord with grounding plug
- Thermostat in primary to prevent overheating
- Resettable circuit breakers in secondary circuit to protect lighting components
- 12v euro style terminal board makes wiring simple and fast
- Operating voltage: 120V input, 12V output, 60hz

Construction

- Black powder coat finish on steel
- Epoxy encapsulated transformer for quiet and cool operation
- Weatherproof construction
- Easy open closure with KO's for photocontrol installation

Mounting

- Vertical mounting
- Top mounting bracket with keyhole slot is attached to housing
- Bottom mounting bracket with slot is attached to housing
- Can be mounted anywhere outdoors

Labeling

- UL-CUL wet location listed
- Made in USA

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607