


Accessory

# 12 Volt Transformers

# **Undercabinet**

Туре		
	-31	
P8652		
P8653		
P8654		
P8655		

	Finish		Dimensions (Inches)		
Catalog No.	Black	Wattage	Α	В	С
P8652	-31	100	3-1/2	3-1/4	8-1/2
P8653	-31	150	4-1/8	3-3/4	8-1/2
P8654	-31	300	4-1/8	4-3/4	8-1/2
P8655	-31	600*	4-5/8	4-1/2	12



### \*2/300w circuits

## Specifications:

#### Electrical

- Dual secondary taps of 12.0 and 12.6 volts
  - Maximizes light output and lamp life under varying load conditions
  - Adjusts for light loss in longer runs
- Isolation type transformer for safe operation
- Loads on P8655 two 300 watt circuits must be balanced for optimum operation
- Thermostat in primary to prevent overheating
- Resettable circuit breakers in secondary circuit to protect lighting components
- Induction type switches and dimmers only must be installed in the primary side

#### Construction

- Black powder coat finish on steel
- Epoxy encapsulated transformer for quiet and cool operation
- Easy open closure with KO's for hardwiring and installation

### Mounting

- · Horizontal or vertical mounting
- Top mounting bracket with keyhole slot is attached to housing
- Can be mounted anywhere indoors

### Labeling

• UL-CUL listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607