


## Incandescent

# 6" Shallow Housing IC & Non-IC

## Recessed

Туре	
P86-TG □	

Catalog No.	Lamping	Dimensions (Inches)	
		A B C	
P86-TG	See Trim Specifications	7-7/8 10-3/4 5-1/2 Ceiling Opening 6-7/8	



## **Specifications:**

#### Wiring

- Universal J-box with snap-out sides
- Removable housing for field inspection of wiring
- Grounding pigtail
- Integral knock out free Romex clamps
- 1/2" & 3/4" knock outs for rigid conduit or BX fittings

#### Construction

- Shallow housing for 2X6 construction
- Notched housing for chalkline alignment
- Overspray protection
- Socket can be used as a temporary work light with an 'A' lamp
- Porcelain socket with nickel-plated brass screw shell
- Housing adjusts from 1/2 " to 1-1/2 " thick ceilings
- Full wrap-around plaster frame
- Removable K.O. for remodel use (P8607-01 plaster frame clips also required)

### **Bar Hangers**

- Integral nailers for wood joist construction
- Integral T-bar mounting clamps
- Span 24" T-bar spacing
- Lock to secure housing
- Captive
- 90-degree mounting for tight spaces

#### **Labeling**

- IC rated for use with baffle and open trims; Non-IC with all other trims
- UL-CUL Listed for damp location and through branch wiring
- Approved for use in New York City per calendar #40330.

## Lamp/Trim

- Socket mounts to trim for optimum performance and consistent lamp position
- Trim-Lok® action forces trim to fit snugly against the ceiling

Progress Lighting
Post Office Box 5704
Spartanburg, South Carolina
29304-5704