

Project:			
Fixture Type:			
Location:			
Contact:			

## P900012-028

## Ridgecrest

Infuse an abundance of sophisticated versatile light to an commercial or residential setting with this brushed nickel four-head track light fixture. Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas. The round ceiling plate, thin metal bar, and light bases are coated in a beautiful satin white finish. Each lamp head features a crisp frosted glass shade for soft, general ambient light.

- Each lamp head features a crisp frosted glass shade for soft, general ambient light.
- The round ceiling plate, thin metal bar, and light bases are coated in a beautiful satin white finish.
- Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas.
- · Ideal for any sitting room, hallway, or foyer.
- $\boldsymbol{\cdot}$  Perfect for transitional or modern settings.
- · Measures 5-inch width by 7-1/8-inch height.
- $\boldsymbol{\cdot}$  Uses four medium base bulbs that are sold separately (60w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- · Includes installation instructions and mounting hardware.
- · Progress Lighting products are designed for exceptional quality, reliability, and functionality.


Category: Directionals
Finish: Satin White (Painted)
Construction: Steel Construction


Glass/Shade: Etched glass Cylindrical Shade

Width: 5 in Height: 7-1/8 in Depth: 26-1/8 in

Etched glass Cylindrical Shade

Width: 3-3/4 in Height: 4-1/2 in





MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity:	CCSAus Damp Location Listed
Canopy 5" W., 0.18" ht., 5" depth	6 inches of wire supplied	Four 60 W max. Medium Base or LED equivalent	1-year Limited Warranty
	120 V	E26 base sockets	