## **PROGRESS** LIGHTING<sup>™</sup>

Project:			
Fixture Type:			
Location:			

Contact:

## P900013-009 Kitson


Incorporate a hint of stylish industrial light to any commercial or residential setting with this brushed nickel one-head track metal directional light fixture. A multi-directional lamp head provides design flexibility and illuminates typically hard-to-reach areas such as highlighting an image in a lobby or gallery. The directional frame is coated in a beautiful brushed nickel finish. The lamp features an industrial styled-shade with an outer ribbed design and the capability to create different beam shapes as needed.


- Each lamp features an industrial styled-shade with an outer ribbed design and the capability to create different beam shapes as needed.
- The directional frame is coated in a beautiful brushed nickel finish.
- Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach
  areas
- Ideal for any lobby, gallery, sitting room, hallway, or foyer.
- · Perfect for transitional or modern settings.
- Measures 5-inch width by 5-15/16-inch height.
- Uses one GU10 base bulb that is sold separately (50w max LED or incandescent).
- Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Directionals Finish: Brushed Nickel (Plated) Construction: Steel Construction



Width: 5 in Height: 5-15/16 in Depth: 5 in





MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or Ceiling mounted	Prewired	Quantity: One 50 W max. MR-16 (GU10,	CCSAus Damp Location Listed
Canopy 5" W., 1.18" ht., 5" depth	6 inches of wire supplied	120V) or LED equivalent	1-year Limited Warranty
	120 V	GU10 base socket	