

Project:		
Fixture Type:		
Location:		
Contact:		

P900014-031

Kitson


Incorporate a hint of stylish industrial light to any commercial or residential setting with this brushed nickel four-head track metal directional light fixture. Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas such as highlighting images in a lobby or gallery. The directional frame is coated in a beautiful black finish. Each lamp features an industrial styled-shade with an outer ribbed design and the capability to create different beam shapes as needed.

- Each lamp features an industrial styled-shade with an outer ribbed design and the capability to create different beam shapes as needed.
- The directional frame is coated in a beautiful black finish.
- Multi-directional lamp heads provide design flexibility and illuminate typically hard-to-reach areas
- · Ideal for any lobby, gallery, sitting room, hallway, or foyer.
- · Perfect for transitional or modern settings.
- Measures 5-inch width by 6-7/16-inch height.
- Uses four GU10 base bulbs that are sold separately (50w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Directionals **Finish:** Black (Painted)

Construction: Steel Construction

Width: 5 in Height: 6-7/16 in Depth: 26-1/8 in





MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall or Ceiling mounted	Prewired	Quantity: Four 50 W max. MR-16 (GU10,	CCSAus Damp Location Listed
Canany F" \\ 110" ht F" donth	6 inches of wire supplied	120V) or LED equivalent	1-year Limited Warranty
Canopy 5" W., 1.18" ht., 5" depth	120 V	GU10 base sockets	