
Alpha Track

Track



Тур	е				
	-09	-10	-28	-31	
P9103					
P9104					
P9105					
P9106					

		Fini	sh				
	Brushed	Polished			Dimensions (Inches)		
Catalog No.	Nickel	Brass	White	Black	А	В	С
P9103	-09	N/A	-28	-31	1-1/8	7/8	24
P9104	-09	-10	-28	-31	1-1/8	7/8	48
P9105	-09	-10	-28	-31	1-1/8	7/8	96
P9106	-09	N/A	-28	-31	1-1/8	7/8	144



Specifications:

Mechanical

- Minimum .050" extruded aluminum housing
- Polarity notch for rows and fitters
- Keyholes and round KO's on top of track for mounting
- Mounting screws and toggle bolts included
- One dead end included
- Can be field cut to desired lengths
- See catalog for available accessories
- Order power feed separately

Electrical

- Single circuit
- 120 volt, 20 ampere capacity
- Flat copper buss bars
- Buss bars enclosed in a non-conducting plastic extrusion

Labeling

• UL-CUL dry location listed

Progress Lighting Post Office Box 5704 Spartanburg, South Carolina 29304-5704