


## Multifamily/Commercial

• Damp Location Listed 

### Description:

LED Commercial Backlit Lay-in Panel - PCIBP-22

### Specifications:

- Diffuse PMMA Flat Panels
- Dimmable to 10% brightness
- 6 in of wire supplied

### Performance:

Input Power	32 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	2,802/3,810/4,290 / 145/142/135 (LM-79)
CCT	3500 K
	4000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cULus Damp Location Listed
Dimming	0-10V dimming
Operating Temperature	-20 °C to 40 °C
THD	<20%
Power Factor	>0.90

## PCIBP-22-LS-CS



### Dimensions:

Square: 23-11/16 in  
Height: 1-1/2 in

