

Project:		
Fixture Type:		
Location:		
Contact:		

# **PECUE SERIES**

# LED Combination Exit/Light

# **Specifications:**

## **Description:**

The PECUE Series offers quality and value with a compact and attractive LED based combination emergency exit. The white housing and lamp-heads are made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face. Remote capacity unit will run 4 PERHC Series single remote lamp-heads or 2 double PERHC remotes.

#### Features:

- · LED life-cycle of more than 10 years
- · Molded-in template for Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting
- Remote capacity option
- Damp Location Listed
- Provided with test switch and AC-On indicator
- · Canopy included

### **Application:**


The PECUE Series can be applied in stair-wells, hallways, offices and other commercial applications

#### **Energy Consumption:**

	120 VAC	277 VAC
UR-30	4.12W	3.20W
UG-30	3.22W	3.18W
UR-30-RC	3.56W	4.06W
UG-30-RC	3.20W	3.80W

#### **Accessories:**

- PERHC SG ID 30
- PERHC DB ID 30
- PERHC SG OD 30














#### Images:



#### **Dimensions:**



#### Warranty:

2 year full unit warranty

#### **Compliances:**

- UL924 Listed for Damp Location
- NFPA 101 and NFPA 70
- OSHA

#### Catalog number:

Base	Material	Face	Color	Finish	Remote Capacity
PECUE	Thermoplastic	<b>U</b> - Universal	R - Red	<b>30</b> - White	RC - Remote Capacity
			G - Green		