

Project:	
Fixture Type:	
Location:	
Contact:	

PERHC SERIES

LED Indoor and Outdoor Remote

Specifications:

Description:

The PERHC Series offers quality and value with a compact and attractive LED based remote emergency light. The white base-plate and lamp—heads are made of high impact UL flame rated thermoplastic. Lamp-heads are fully adjustable and glare-free. The remote lamps are driven by the Progress remote capacity Exit combo or Emergency Light. The Outdoor Remote lamp-heads are fully gasketed and weatherproof to ensure operation in wet environments.

Features:

- · LED life-cycle of more than 10 years
- · Single or Double lamp-head remote with base-plate
- · Quick installation
- Damp location listed (Indoor)
- · Fully gasketed for application in wet environment (Outdoor)
- · Fully adjustable lamp-heads
- 3 VDC
- · 1 Watt per lamp

Application:

The PERHC Series can be applied in stair-wells, hallways, offices and other commercial applications (Indoor) or over path of egress doors and in areas affected by rain, moisture and condensation.

Compliances:

- · UL924 Listed for Damp Location (Indoor)
- NFPA 101 and NFPA 70
- · OSHA


Warranty:

2 year full unit warranty

Images:



Dimensions:



Catalog number:

Base	Lamp	Location	Finish
PERHC	SG - Single	ID - Indoor	30 - White
	DB - Double	OD - Outdoor	