

Fixture Type: Location:

Contact:

PETPE SERIES

LED Emergency Exit

Specifications:

Description:

The PETPE Series offers quality and value with a compact and attractive LED based emergency exit. The white housing is made of high impact UL flame rated thermoplastic. Snap together canopy, housing, removable chevrons for quick and easy installation. Universal single or double-face. Remote capacity option will run 4 PERHC Series single remote lamp-heads or 2 double PERHC remotes.

Features:

- LED life-cycle of more than 10 years
- · Molded-in template for Quick installation
- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90 minute emergency lighting •
- Remote capacity option •
- Damp Location Listed .
- Provided with test switch and AC-On indicator .
- . Canopy included

Application:

The PETPE Series can be applied in stair-wells, hallways, offices and other commercial applications

	120 VAC	277 VAC
UR-30	1.78W	1.88W
UG-30	1.49W	1.57W
UR-30-RC	3.60W	4.14W
UG-30-RC	3.28W	3.81W

Accessories:

- . PERHC - SG - ID - 30
- PERHC DB ID 30 .
- PERHC SG OD 30
- PERHC DB OD 30

Catalog number:






Images:



PETPE-UR-30

PETPE-UG-30

Dimensions:



Warranty:

2 year full unit warranty

Compliances:

- UL924 Listed for Damp Location
- NFPA 101 and NFPA 70
- . OSHA

8					
Base	Material	Face	Color	Finish	Remote Capacity
PE	TPE - Thermoplastic	U - Universal	R - Red	30 - White	RC - Remote Capacity
	·		G - Green		