

Multifamily/Commercial

• Wet Location Listed **PROGRESS LED**

Description:

LED Outdoor Commercial Bollard - PMBO

Specifications:

- Clear Polycarbonate Cylindrical
- Dimmable to 10% brightness (See Dimming Notes)
- 6 in of wire supplied

Performance:

Input Power	20 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	1,522/76.1 (LM-79)
CCT	4000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Part 15, Class A
Warranty	5-year Limited Warranty
Labels	cETLus Wet Location Listed
Dimming	0-10V dimming
Operating Temperature	-20 °C to 40 °C
THD	<20%
Power Factor	>0.90

PMBOR-DMT-4K-BL



Dimensions:

Diameter: 6-1/2 in
Height: 39-3/4 in

