


## Multifamily/Commercial

• Damp Location Listed 

### Description:

LED Commercial Economy Wrap Light - PMIEW

### Specifications:

- Diffuse Polycarbonate Wrap Around Lens
- Dimmable to 10% brightness
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

### Performance:

Input Power	45 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	3,925/5,017/5,880 / 131/128/131 (LM-79)
CCT	3500 K
	4000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Part 15, Class A
Warranty	5-year Limited Warranty
Labels	cULus Damp Location Listed
Dimming	0-10V dimming
Operating Temperature	-25 °C to 50 °C
THD	<20%
Power Factor	>0.90

## PMIEW-4-LS-CS



### Dimensions:

Length: 47-1/2 in  
Width: 5-3/8 in  
Height: 2 in

