


Multifamily/Commercial

• Wet Location Listed 

Description:

LED Commercial Vapor Tight Strip Light - PMIVT

Specifications:

- Diffuse Polycarbonate Half Cylinder
- Dimmable to 10% brightness
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Input Power	51 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	5,603/6,198/7,611 / 146/144/149 (LM-79)
CCT	3500 K
	4000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Part 15, Class A
Warranty	5-year Limited Warranty
Labels	cULus Wet Location Listed
Dimming	0-10V dimming
Operating Temperature	-40 °C to 40 °C
THD	<20%
Power Factor	>0.90

PMIVT-4-LS-CS



Dimensions:

Length: 47 in
Width: 3-3/4 in
Height: 3 in

