

Multifamily/Commercial

• Wet Location Listed **PROGRESS LED**

Description:

LED Outdoor Commercial Garage/Canopy Light - PMOCL

Specifications:

- Clear Polycarbonate Square/Rectangular
- Dimmable to 10% brightness
- Fixture covers a standard 4" recessed outlet box
- 6 in of wire supplied

Performance:

Input Power	73 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	6,962/8,248/10,506 / 163/161/152 (LM-79)
CCT	3000 K
	4000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cULus Wet Location Listed
Dimming	0-10V dimming
Operating Temperature	-40 °C to 40 °C
THD	<20%
Power Factor	>0.90

PMOCL-LS-CS-BZ



Dimensions:

Length: 10-1/2 in
Width: 9-1/2 in
Height: 2-15/16 in

