

Multifamily/Commercial

Wall Mounted • Wet Location Listed **PROGRESS LED**

Description:

LED Outdoor Commercial Floodlight - PMOFL

Specifications:

- Rugged die-cast aluminum housing
- Dark Bronze powder coat finish with polycarbonate lens
- Wide flood NEMA 7x7 distribution for general purpose flood
- CCT field selectable feature offers 3000K, 4000K and 5000K options

Performance:

Input Power	16 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	2,175/125 (LM-79)
Lumen value based on 4000K selection	
CRI	80 CRI
Life (hours)	50000
EMI/RFI	FCC Part 15, Class A
Warranty	5-year Limited Warranty
Labels	cULus Wet Location Listed
Dimming	0-10VDC
Ingress Protection	IP65
Operating Temperature	-40 °C to 50 °C
THD	<20%
Power Factor	>0.90

	CCT Selection		
	3000K	4000K	5000K
Watts	16W	15W	16W
Lumens	2002	2179	2085
Efficacy	125	145	132

PMOFL-1-LS-CS-BZ



Dimensions:

Length: 4-1/4 in
 Width: 1-11/16 in
 Height: 5-3/4 in

