

Multifamily/Commercial

• Wet Location Listed 

Description:

LED Outdoor Commercial Trapezoid Wall Pack - PMOWF-1

Specifications:

- Clear Polycarbonate Square/Rectangular
- Dimmable to 10% brightness
- 6 in of wire supplied

Performance:

Input Power	57 W
Input Voltage	Universal 120-277 VAC
Input Frequency	50/60 Hz
Lumens/LPW (Delivered)	5,526/7,048/8,682 / 161//156/152 (LM-79)
CCT	3000 K
	4000 K
	5000 K
CRI	80 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cULus Wet Location Listed
Dimming	0-10V dimming
Operating Temperature	-40 °C to 45 °C
THD	<20%
Power Factor	>0.90

PMOWF-1-LS-CS-P-BZ



Dimensions:

Length: 14 in
Width: 6 in
Height: 9 in

