



\* Representative image

## BOLT, SPOOL, SINGLE-UPSET, 5/8in x 18in

by CHANCE Utility  
Catalog ID: PS7746

Single-upset spool bolt, 5/8" diameter x 18" shank length, with 6" thread length and cone pointed end. Overall length is 22 3/4". Includes one square nut with cotter key. Rated cantilever load is 1,900 lbs. Hot dip galvanized per ASTM A-153. Manufactured in compliance with ANSI C135.31. RUS listed, q - Bolt, double upset.

### Product Details

#### General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb
Type	Spool Bolts
UPC	096359565123

#### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	18.00 in
Weight	2.02 lb

#### Logistics

Carton Quantity	20 EA
-----------------	-------

**For further technical assistance, please contact us**

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)