



PTOB1150010LS

by Acme Electric
Catalog ID: PTOB1150010LS

Panel Tran Zone Power Centers - Single Phase, 480 - 120/240V, 10kVA,
Bolt In Breakers

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

Product Details

General

ANFC Taps	-
BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Breaker	ED42B035L (35A)
Primary Voltage	480
Product Category	Panel-Tran Zone Power Centers
Secondary Breaker	B250H (50A)
Secondary Voltage	120/240 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503090305
Winding Material	AL
kVA	10

Dimensions

Height	34.38 in
Length	12.38 in
Weight	185 lb
Width	17.13 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480 V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 1062