



PTBB3150022SS

by Acme Electric
Catalog ID: PTBB3150022SS

Panel Tran Zone Power Centers - Three Phase, 480Δ - 208Y/120V,
22.5kVA, Bolt In Breakers, 304 Stainless Steel

- Fully compliant with NEC 450-3
- Designed for indoor and outdoor applications
- Electrostatic shield for enhanced protection
- Primary and Secondary main circuit breakers provided

Product Details

General

ANFC Taps	-
BNFC Taps	2
Construction	Encapsulated
Electrostatic Shield	Shielded
Max Temperature Rise	115 Degrees Celsius
Mounting Type	Wall
Primary Breaker	ED43B070L (70A)
Primary Voltage	480
Product Category	Panel-Tran Zone Power Centers
Secondary Breaker	B370 (70A)
Secondary Voltage	208Y/120 V
Taps % Steps	5%
UL Insulation Class	180°C
UPC	047503090343
Winding Material	CU
kVA	22.5

Dimensions

Height	43.75 in
Length	13.75 in
Weight	535 lb
Width	33 in

Electrical Ratings

Frequency Rating	60 Hz
Primary Voltage	480D V

Certifications and Compliance

CSA Standard	C22.2 No 47
Nema Rating	NEMA 3R
UL Standard	UL 1062