

Type GL Resistor

By Powerohm Resistors
Catalog # [GL41-T](#)



Type GL Triple Grid Resistor 15.3 ohms 41 A

Features

- Insulated for 1000V
- Can be used AC/DC application
- Standard tolerance +/-10%
- 26.5"WX29"Dx6"H
- 120 LBS EA

General

Catalog Number	GL41-T
Resistance Ohms	15.3 Ohm
Type	Grid Resistor Type GL

Dimensions

Depth	6 in
Length	26.5 in
Weight	89 lb
Width	27.75 in

Electrical Ratings

Current / Amperage Rating	41 A
Maximum Current Rating Amps	41 Amps
Continuous	
Wattage	25719 W

Product Assets

[Specifications - GL41-T](#)