

# Type GL Resistor

By Powerohm Resistors  
Catalog # [GL80-D](#)



Type GL Double Grid Resistor 2.06 ohms 80 A

## Features

- Insulated for 1000V
- Can be used AC/DC application
- Standard tolerance +/-10%
- 26.5"WX21.5"Dx6"H
- 80 LBS EA

## General

|                 |                       |
|-----------------|-----------------------|
| Catalog Number  | GL80-D                |
| Resistance Ohms | 2.06 Ohm              |
| Type            | Grid Resistor Type GL |

## Dimensions

|        |           |
|--------|-----------|
| Depth  | 6 in      |
| Length | 26.5 in   |
| Weight | 60 lb     |
| Width  | 19.437 in |

## Electrical Ratings

|                             |         |
|-----------------------------|---------|
| Current / Amperage Rating   | 80 A    |
| Maximum Current Rating Amps | 80 Amps |
| Continuous                  |         |
| Wattage                     | 13184 W |

## Product Assets

[Specifications - GL80-D](#)