

## PREWR4-38 | Replacement Part

By Powerohm  
Catalog # [PREWR4-38](#)



IPC Replacement Part, EW Edgewound Resistor, 0.38 Ohms,  
47 A, MFG Part Number-EWR4-38

### Features

- IPC MFG Part Number-EWR4-38

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.38 Ohm
Type	Edgewound Type EW

### Dimensions

Length	4 in
--------	------

### Electrical Ratings

Current / Amperage Rating	47 A
Maximum Current Rating Amps Continuous	47 Amps