

## PREWR8-40 | Replacement Part

By Powerohm  
Catalog # [PREWR8-40](#)



IPC Replacement Part, EW Edgewound Resistor, 0.4 Ohms, 70 A, MFG Part Number-EWR8-40

### Features

- IPC MFG Part Number-EWR8-40

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.4 Ohm
Type	Edgewound Type EW

### Dimensions

Length	8 in
--------	------

### Electrical Ratings

Current / Amperage Rating	70 A
Maximum Current Rating Amps Continuous	70 Amps