

PRFH37 | Replacement Part

By Powerohm
Catalog # [PRFH37](#)



Filnor Replacement Part, Type GL Grid Resistor, 6.09 Ohms, 37 A, MFG Part Number-FH37

Features

- Filnor MFG Part Number-FH37

Application

Filnor

General

Maximum Temperature Rise	375 °C
Resistance Ohms	6.09 Ohm
Type	Grid Resistor Type GL

Dimensions

Length	26.5 in
Weight	29 lb

Electrical Ratings

Current / Amperage Rating	37 A
Maximum Current Rating Amps Continuous	37 Amps