

PRFT120 | Replacement Part

By Powerohm
Catalog # [PRFT120](#)



Filnor Replacement Part, Type GL Grid Resistor, 0.421 Ohms,
120 A, MFG Part Number-FT120

Features

- Filnor MFG Part Number-FT120

Application

Filnor

General

| | |
|--------------------------|-----------------------|
| Maximum Temperature Rise | 375 °C |
| Resistance Ohms | 0.421 Ohm |
| Type | Grid Resistor Type GL |

Dimensions

| | |
|--------|---------|
| Length | 26.5 in |
| Weight | 29 lb |

Electrical Ratings

| | |
|---|----------|
| Current / Amperage Rating | 120 A |
| Maximum Current Rating Amps Continuous | 120 Amps |