

## PRG015H-G | Replacement Part

By Powerohm Resistors  
Catalog # [PRG015H-G](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.63 Ohms, 91 A, MFG Part Number-G015H-G

### Features

Post Glover Replacement PartNumber-G015H-G

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.63 Ohm
Type	Grid Resistor Type T2 & H3

### Dimensions

Length	26.5 in
--------	---------

### Electrical Ratings

Current / Amperage Rating	91 A
Maximum Current Rating Amps	91 Amps
Continuous	
Wattage	5217 W

### Product Assets