

PRG026G | Replacement Part

By Powerohm Resistors
Catalog # [PRG026G](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.7 Ohms, 80 A, MFG Part Number-G026G

Features

Post Glover Replacement PartNumber-G026G

General

Catalog Number	PRG026G
Maximum Temperature Rise	375 °C
Resistance Ohms	0.7 Ohm
Type	Grid Resistor Type T2 & H3

Dimensions

Length	22.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	80 A
Maximum Current Rating Amps	80 Amps
Continuous	
Wattage	4480 W

Product Assets

[Specifications - PRG026G](#)