

## PRG026G | Replacement Part

By Powerohm Resistors  
Catalog # [PRG026G](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.7 Ohms, 80 A, MFG Part Number-G026G

### Features

Post Glover Replacement PartNumber-G026G

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.7 Ohm
Type	Grid Resistor Type T2 & H3

### Dimensions

Length	22.5 in
--------	---------

### Electrical Ratings

Current / Amperage Rating	80 A
Maximum Current Rating Amps	80 Amps
Continuous	
Wattage	4480 W

### Product Assets