

PRG028 | Replacement Part

By Powerohm
Catalog # [PRG028](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 1.836 Ohms,
57 A, MFG Part Number-G028

Features

- Post Glover Replacement PartNumber-G028

General

Maximum Temperature Rise	375 °C
Resistance Ohms	1.836 Ohm
Type	Grid Resistor Type T2 & H3

Dimensions

Length	22.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	57 A
Maximum Current Rating Amps Continuous	57 Amps
Wattage	5965 W