

## PRG23H | Replacement Part

By Powerohm Resistors

Catalog # [PRG23H](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.308 Ohms,  
120 A, MFG Part Number-G23H

### Features

Post Glover Replacement PartNumber-G23H

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.308 Ohm
Type	Grid Resistor Type T2 & H3

### Dimensions

Length	22.5 in
--------	---------

### Electrical Ratings

Current / Amperage Rating	120 A
Maximum Current Rating Amps	120 Amps
Continuous	
Wattage	4435 W

### Product Assets