

PRG33R | Replacement Part

By Powerohm Resistors

Catalog # [PRG33R](#)

Post Glover Replacement Part, HC Ribbon Resistor, 0.115 Ohms,
450 A, MFG Part Number-G33R



Features

Post Glover Replacement PartNumber-G33R

General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.115 Ohm
Type	HC Wide Strip Resistor Type

Dimensions

Length	22.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	450 A
Maximum Current Rating Amps	450 Amps
Continuous	
Wattage	23288 W

Product Assets