

PRG59R-G | Replacement Part

By Powerohm Resistors
Catalog # [PRG59R-G](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.29 Ohms,
135 A, MFG Part Number-G59R-G

Features

Post Glover Replacement PartNumber-G59R-G

General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.29 Ohm
Type	Grid Resistor Type T2 & H3

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	135 A
Maximum Current Rating Amps	135 Amps
Continuous	
Wattage	5285 W

Product Assets