

PRG79R | Replacement Part

By Powerohm Resistors

Catalog # [PRG79R](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.288 Ohms,
135 A, MFG Part Number-G79R

Features

Post Glover Replacement PartNumber-G79R

General

| | |
|--------------------------|----------------------------|
| Maximum Temperature Rise | 375 °C |
| Resistance Ohms | 0.288 Ohm |
| Type | Grid Resistor Type T2 & H3 |

Dimensions

| | |
|--------|---------|
| Length | 26.5 in |
|--------|---------|

Electrical Ratings

| | |
|-----------------------------|----------|
| Current / Amperage Rating | 135 A |
| Maximum Current Rating Amps | 135 Amps |
| Continuous | |
| Wattage | 5249 W |

Product Assets