

# PRG79R | Replacement Part

By Powerohm Resistors  
Catalog # [PRG79R](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.288 Ohms, 135 A, MFG Part Number-G79R

## Features

Post Glover Replacement PartNumber-G79R

## General

Catalog Number	PRG79R
Maximum Temperature Rise	375 °C
Resistance Ohms	0.288 Ohm
Type	Grid Resistor Type T2 & H3

## Dimensions

Length26.5 in

## Electrical Ratings

Current / Amperage Rating	135 A
Maximum Current Rating Amps	135 Amps
Continuous	
Wattage	5249 W

## Product Assets

[Specifications - PRG79R](#)