

PRMRCG-25 | Replacement Part

By Powerohm
Catalog # [PRMRCG-25](#)



Milwaukee Replacement Part, Grid Resistor, 0.9 Ohms, 80 A,
MFG Part Number-MRCG-25

Features

- Milwaukee MFG Part Number-MRCG-25

Application

Milwaukee

General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.9 Ohm
Type	Grid Resistor Type GL

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	80 A
Maximum Current Rating	80 Amps
Amps Continuous	