

## PRMRCG-24 | Replacement Part

By Powerohm Resistors  
Catalog # [PRMRCG-24](#)



Milwaukee Replacement Part, Grid Resistor, 0.756 Ohms, 90 A,  
MFG Part Number-MRCG-24

### Features

Milwaukee MFG Part Number-MRCG-24

### General

|                          |                       |
|--------------------------|-----------------------|
| Application              | Milwaukee             |
| Maximum Temperature Rise | 375 °C                |
| Resistance Ohms          | 0.756 Ohm             |
| Type                     | Grid Resistor Type GL |

### Dimensions

|        |         |
|--------|---------|
| Length | 26.5 in |
|--------|---------|

### Electrical Ratings

|                             |         |
|-----------------------------|---------|
| Current / Amperage Rating   | 90 A    |
| Maximum Current Rating Amps | 90 Amps |
| Continuous                  |         |

### Product Assets