

## PRPG-29 | Replacement Part

By Powerohm  
Catalog # [PRPG-29](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 1.55 Ohms,  
70 A, MFG Part Number-PG-29

### Features

- Post Glover Replacement PartNumber-PG-29

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	1.55 Ohm
Type	Grid Resistor Type T2 & H3

### Dimensions

Length	26.5 in
--------	---------

### Electrical Ratings

Current / Amperage Rating	70 A
Maximum Current Rating Amps Continuous	70 Amps
Wattage	7595 W