

## PRPG-38 | Replacement Part

By Powerohm  
Catalog # [PRPG-38](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 10.08 Ohms, 25 A, MFG Part Number-PG-38

### Features

- Post Glover Replacement PartNumber-PG-38

### General

Maximum Temperature Rise	375 °C
Resistance Ohms	10.08 Ohm
Type	Grid Resistor Type T2 & H3

### Dimensions

Length	26.5 in
--------	---------

### Electrical Ratings

Current / Amperage Rating	25 A
Maximum Current Rating Amps Continuous	25 Amps
Wattage	6300 W