

PRPG-12 | Replacement Part

By Powerohm Resistors
Catalog # [PRPG-12](#)



Post Glover Replacement Part, HC Ribbon Resistor, 0.144 Ohms,
225 A, MFG Part Number-PG-12

Features

Post Glover Replacement PartNumber-PG-12

General

Catalog Number	PRPG-12
Maximum Temperature Rise	375 °C
Resistance Ohms	0.144 Ohm
Type	HC Wide Strip Resistor Type

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	225 A
Maximum Current Rating Amps	225 Amps
Continuous	
Wattage	7290 W

Product Assets

[Specifications - PRPG12](#)