

PRPG-23 | Replacement Part

By Powerohm Resistors

Catalog # [PRPG-23](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.648 Ohms,
100 A, MFG Part Number-PG-23

Features

Post Glover Replacement PartNumber-PG-23

General

Maximum Temperature Rise	375 °C
Resistance Ohms	0.648 Ohm
Type	Grid Resistor Type T2 & H3

Dimensions

Length	26.5 in
--------	---------

Electrical Ratings

Current / Amperage Rating	100 A
Maximum Current Rating Amps	100 Amps
Continuous	
Wattage	6480 W

Product Assets