

# PRPG-24 | Replacement Part

By Powerohm Resistors  
Catalog # [PRPG-24](#)



Post Glover Replacement Part, T2H3 Grid Resistor, 0.756 Ohms,  
90 A, MFG Part Number-PG-24

## Features

Post Glover Replacement PartNumber-PG-24

## General

Catalog Number	PRPG-24
Maximum Temperature Rise	375 °C
Resistance Ohms	0.756 Ohm
Type	Grid Resistor Type T2 & H3

## Dimensions

Length26.5 in

## Electrical Ratings

Current / Amperage Rating	90 A
Maximum Current Rating Amps	90 Amps
Continuous	
Wattage	6124 W

## Product Assets

[Specifications - PRPG24](#)